


Grundmodelle



<b>OT6</b>	OT6.01	OT6.02	OT6.03	OT6.04	OT6.05
<b>OT4</b>	OT4.01	OT4.02	OT4.03	OT4.04	OT4.05

Mit Lichtaus-schnitten



<b>OT6</b>	OT6.01 L	OT6.02 L	OT6.03 L1	OT6.03 L3	OT6.04 L1	OT6.04 L4	OT6.05 L2
<b>OT4</b>	OT4.01 L	OT4.02 L	OT4.03 L1	OT4.03 L3	OT4.04 L1	OT4.04 L4	OT4.05 L2

Merkmale



OT6. – das Profil (60 mm)



OT4. – das Profil (40 mm)



Glasleiste OT6. L und OT4. L (25 mm)

1. Fräsung: Tiefe 4 mm, Profil: **OT6.**: 60 mm, Glasleiste: **OT6. L** 25 mm  
Profil: **OT4.**: 40 mm, Glasleiste: **OT4. L** 25 mm
2. korrespondierendes Leistenbild bei Lichtausschnitten
3. Glasrahmen aus einem Stück gefräst
4. gefälzt oder stumpf mit verdeckten Bändern
5. gerader Überschlag, Kanten gebrochen
6. passende Zargen: E, S 70, duo 55, duo 70, duo 90

Passende Zarge



Zarge E



Zarge S 70



Zarge duo 55



Zarge duo 70



Zarge duo 90